



FITCR10C10B  
...  
FITCR22C25B



FITCR40C10B  
FITCR40C25B



Todos los cartuchos llevan  
bypass.

Apertura válvula bypass: 1 bar

| Artículo           | Detalles     | Caudal máx.<br>(l/min) | ØB   | ØD  | H   |
|--------------------|--------------|------------------------|------|-----|-----|
| <b>FITCR10C10B</b> | Cartón 10 µm | 50                     | 25,5 | 52  | 72  |
| <b>FITCR10C25B</b> | Cartón 25 µm | 50                     | 25,5 | 52  | 72  |
| <b>FITCR20C10B</b> | Cartón 10 µm | 100                    | 30,5 | 66  | 85  |
| <b>FITCR20C25B</b> | Cartón 25 µm | 100                    | 30,5 | 66  | 85  |
| <b>FITCR22C10B</b> | Cartón 10 µm | 100                    | 30,5 | 66  | 130 |
| <b>FITCR22C25B</b> | Cartón 25 µm | 100                    | 30,5 | 66  | 130 |
| <b>FITCR40C10B</b> | Cartón 10 µm | 250                    | 41   | 100 | 220 |
| <b>FITCR40C25B</b> | Cartón 25 µm | 250                    | 41   | 100 | 220 |

TOL--> ØB:±0,3; ØD:±0,5; H:±1,6